Rittal – The System.

Faster – better – everywhere.



AS 4050.451

Stripping machine S22

State: 11/14/2026 (Source: www.rittal.com/us-en)

AS 4050.451 - Stripping machine S22

Semi-automatic machine for stripping wires in various cross-sectional areas

Features

Model No.	AS 4050.451
Version	Touchscreen display Integrated total quantity counter Integrated daily quantity counter Linear adjustment of the wire stripping length
Product description	Semi-automatic machine for stripping wires in various cross-sectional areas.
Benefits	Easy adjustment of cross section with a rotary knob Easy insertion of wires Easy to operate
Technical specifications	Electrically powered Wire stripping range 0.05 - 6 mm² (AWG 30 - 10) Insulation stripping length 3 - 20 mm (0.12 - 0.79 in.) Stripping length 3 - 20 mm (0.12 - 0.79 in.) Insertion length 22 mm (0.87 in.)
Supply includes	Stripping machine S22 Special funnel for inserting thin conductors Replacement blade
Dimensions	Width: 190 mm Height: 190 mm Depth: 295 mm Width: 7.48 ″ Height: 7.48 ″ Depth: 11.6 ″
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	70 VA
Cycle time	0.5 s
Packaging unit	1 pc(s).

© Rittal 2026

Features

Net weight	8.5 kg
Gross weight	9.06 kg
Customs tariff number	84798997
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36629090
Product description	Stripping machine S 22, 0,05-6mm²