Rittal – The System.

Faster – better – everywhere.





AS 4050.456 Automatic Crimping Machine RC

State: 11/15/2025 (Source: rittal.com/us-en)



AS 4050.456 - Automatic Crimping Machine RC

Electro-pneumatic automatic crimping machine with five-fold magazine for processing insulated wire end ferrules in different cross-sections on coils.

Features

| Model No. | AS 4050.456 |
|---------------------------|--|
| Version | Touchscreen display Selection of wire cross-section via touchscreen Support can be fitted with a maximum of 23,000 wire-end ferrules |
| Product description | |
| Benefits | Easy operation Secure, fast processing of insulated wire end ferrules No set-up time thanks to automatic tool change Simple, quick component mounting No need to change the wire-end ferrules thanks to the 5-way assembly |
| Technical specifications | Crimping range 0.5–2.5 mm² (AWG 20 - 14) 8 and 10 mm crimping lengths Insertion length 27 mm (1.06 in.) |
| Note | Standard crimping shape, trapezium - others available upon request |
| Dimensions | Width: 335 mm Height: 565 mm Depth: 485 mm Width: 13.2 " Height: 22.2 " Depth: 19.1 " |
| Compressed air connection | 5.5 bar |
| Rated operating voltage | 100 V - 240 V, 1~, 50 Hz/60 Hz |
| Apparent power | 16 VA |
| Crimping | Trapezoid crimp |
| Cycle time | 2 s |

© Rittal 2025

Features

| Packaging unit | 1 pc(s). |
|-----------------------|---------------|
| Net weight | 24.8 |
| Gross weight | 25.4 |
| Customs tariff number | 84624900 |
| EAN | 4028177930865 |
| ETIM 9 | EC002778 |
| ETIM 8 | EC002778 |
| ECLASS 8.0 | 17130101 |

© Rittal 2025 3