Rittal – The System.

Faster – better – everywhere.



AS 4050.456
Automatic Crimping Machine RC

State: 11/10/2026 (Source: www.rittal.com/us-en)

AS 4050.456 - Automatic Crimping Machine RC

Electro-pneumatic automatic crimping machine with five-fold magazine for processing insulated wire end ferrules in different cross-sections on coils.



Features

Model No.	AS 4050.456
Version	Touchscreen display Selection of wire cross-section via touchscreen Support can be fitted with a maximum of 23,000 wire-end ferrules
Product description	
Benefits	Easy operation Secure, fast processing of insulated wire end ferrules No set-up time thanks to automatic tool change Simple, quick component mounting No need to change the wire-end ferrules thanks to the 5-way assembly
Technical specifications	Cross-sections ranging from 0.5–2.5 mm² (AWG 20–14) 8 and 10 mm crimping lengths Insertion length 27 mm (1.06 in.)
Note	Standard crimping shape, trapezium - others available upon request
Dimensions	Width: 335 mm Height: 565 mm Depth: 485 mm Width: 13.2 ″ Height: 22.2 ″ Depth: 19.1 ″
Compressed air connection	5.5 bar

© Rittal 2026

Features

Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	16 VA
Crimping	Trapezoid crimp
Cycle time	2 s
Packaging unit	1 pc(s).
Net weight	24.8 kg
Gross weight	25.4 kg
Customs tariff number	84624900
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	17130101
Product description	RC crimping machine, insulation stripping and crimping, for processing 5 wire end ferrules