


Rittal – The System.

Faster – better – everywhere.



AS 4050.747

Wire end ferrule

State: 5/22/2024 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.747 - Wire end ferrule on belt

With plastic flange.

Features

Model No.	AS 4050.747
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Gray
Length	8 mm 0.31 ~
AWG	18
Internal diameter	2.8 mm 0.11 ~
For cross section	0.75 mm ²
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packaging unit	5,000 pc(s).
Weight/packaging unit	5 kg 11 lb.
Customs tariff number	85369010
EAN	4028177805156
ETIM 7.0	EC000005
ECLASS 8.0	36659290

Approvals

Approvals

UL + C-UL (listed)

UR