Rittal - The System.

Faster - better - everywhere.





SK 3340.230

Rack-mounted fans for 482.6 mm (19")

State: 10/31/2025 (Source: rittal.com/us-en)



SK 3340.230 - Rack-mounted fans for 482.6 mm (19") Air throughput 188.34 - 282..52 cfm

Rack-mounted fan for direct installation in the 19" level. Installation allows air to circulate permanently inside the enclosure, which prevents the creation of hot spots.

Features

Model No.	SK 3340.230
Product description	Rack-mounted fan for direct installation in the 19" level. The installation enables permanent air circulation in the enclosure, which prevents the creation of hot spots.
Color	RAL 7035
Supply includes	Wired unit ready for connection Incl. terminal strip and assembly components
Air throughput (unimpeded air flow)	320 m³/h 188.3 cfm
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 0.24 A At 60 Hz: 0.22 A
Pre-fuse	Miniature circuit-breaker/fuse: 6 A
Dimensions	Width: 482.6 mm Height: 44 mm Depth: 200 mm Width: 19 " Height: 1.73 " Depth: 7.87 "
Distance between fan axes	85 mm 3.35 ″
Number of fans	2
Noise pressure level	At 50 Hz: 51 dB(A)
Operating temperature range	-10 °C55 °C 14 °F131 °F

© Rittal 2025 2

Features

Packaging unit	1 pc(s).
Net weight	2.04
Gross weight	2.2
Customs tariff number	84145915
EAN	4028177041448
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Approvals	UR + C-UR (recognized) VDE
Explanations	Declaration of conformity

© Rittal 2025 3