

# Rittal – The System.

Faster – better – everywhere.



## SK 3341.115

# Rack-mounted fans for 482.6 mm (19")

State: 6/10/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3341.115 - Rack-mounted fans for 482.6 mm (19") Air throughput 188.34 - 282..52 cfm

Rack-mounted fan for direct installation in the 19" level. Installation allows air to circulate permanently inside the enclosure, which prevents the creation of hot spots.

## Features

Model No.	SK 3341.115
Product description	Rack-mounted fan for direct installation in the 19" level. The installation enables permanent air circulation in the enclosure, which prevents the creation of hot spots.
Color	RAL 7035
Supply includes	Wired unit ready for connection Incl. terminal strip and assembly components
Air throughput (unimpeded air flow)	480 m <sup>3</sup> /h 282.5 cfm
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz 110 V (DC)
Rated current max.	At 50 Hz: 0.69 A At 60 Hz: 0.69 A
Pre-fuse	Miniature circuit-breaker/fuse: 6 A
Dimensions	Width: 482.6 mm Height: 44 mm Depth: 200 mm Width: 19 " Height: 1.73 " Depth: 7.87 "
Distance between fan axes	85 mm 3.35 "
Number of fans	3
Noise pressure level	At 50 Hz: 52 dB(A)

## Features

---

Operating temperature range	-10 °C...55 °C 14 °F...131 °F
Packaging unit	1 pc(s).
Net weight	2 kg
Gross weight	2.74 kg
Customs tariff number	84145915
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716
Product description	SK rack-mounted fan, for 482.6 mm (19"), 282.5 cfm 115 V, 1~, 50/60 Hz, WHD: 482.6 x 44 x 200 mm

---

## Approvals

---

Approvals	UR + C-UR (recognized) VDE
Explanations	Declaration of conformity

---