Rittal – The System.

Faster – better – everywhere.



AS 4050.802

Twist drill

State: 11/9/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AS 4050.802 - Twist drill

Machine twist drill for Perforex machining centers BC and Perforex Milling Terminals MT S.

Features

Model No.	AS 4050.802
Version	HSS TiN coating
Product description	Machine twist drill for Perforex machining center BC and Perforex Milling Terminal MT.
Diameter	3.3 mm 0.13 ″
Workable material	Steel Stainless steel Aluminum Plastic Copper
Packaging unit	10 pc(s).
Net weight	0.04 kg
Gross weight	0.049 kg
Customs tariff number	82051000
ETIM 9	EC000945
ETIM 8	EC000945
ECLASS 8.0	36609207
Product description	Drill A002- 3,3mm

© Rittal 2026