Rittal – The System.

Faster – better – everywhere.



AS 4050.807

Twist drill

State: 10/30/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AS 4050.807 - Twist drill

Machine twist drill for Perforex machining centers BC and Perforex Milling Terminals MT S.

Features

Model No.	AS 4050.807
Version	HSS TiN coating
Product description	Machine twist drill for Perforex machining center BC and Perforex Milling Terminal MT.
Diameter	8.5 mm 0.33 ″
Suitable for Model No.	4050107 4050108 4050230
Workable material	Steel Stainless steel Aluminum Plastic Copper
Packaging unit	10 pc(s).
Net weight	0.41 kg
Gross weight	0.42 kg
Customs tariff number	82051000
ETIM 9	EC000945
ETIM 8	EC000945
ECLASS 8.0	36609207
Product description	Twist drill A002, 8. 5mm, packs of 10

© Rittal 2026