Rittal – The System.

Faster – better – everywhere.





AS 4051.548 Wire end ferrule

State: 11/18/2025 (Source: rittal.com/us-en)



AS 4051.548 - Wire end ferrule on belt

With plastic flange.

Features

| Model No. | AS 4051.548 |
|--------------------------|--|
| Product description | With plastic flange. |
| Technical specifications | Heat resistant up to 105 °C |
| Material | E-Cu, tin-plated Plastic collar: Polypropylene |
| Color | White |
| Length | 8 mm 0.31 ″ |
| AWG | 20 |
| Internal diameter | 2.9 mm 0.11 ″ |
| For cross section | 0.5 mm² |
| DIN color code | Yes |
| Multinorm | Yes |
| Note | UL-certified in conjunction with the relevant tools, e.g. crimping machines. |
| Delivery form | Taped |
| Packaging unit | 4,000 pc(s). |
| Net weight | 4 |
| Gross weight | 0.46 |
| Customs tariff number | 85369010 |
| EAN | 4028177937963 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |
| | |

© Rittal 2025

Features

ECLASS 8.0 36659290

Approvals

Approvals UL + C-UL (listed)

© Rittal 2025

3