
Rittal – The System.

Faster – better – everywhere.



# AS 4051.600
# Wire end ferrule

State: 11/12/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# AS 4051.600 - Wire end ferrule on belt

With plastic flange.

## Features

| | |
|---|---|
| Model No. | AS 4051.600 |
| Product description | With plastic flange. |
| Technical specifications | Heat resistant up to 105 °C |
| Material | E-Cu, tin-plated<br>Plastic collar: Polypropylene |
| Color | White |
| Length | 10 mm<br>0.39 ″ |
| AWG | 18 |
| Internal diameter | 2.8 mm<br>0.11 ″ |
| Rittal color code | Yes |
| For cross section | 0.75 mm² |
| Note | UL-certified in conjunction with the relevant tools, e.g. crimping machines. |
| Standards | AEH DIN 46228 |
| Delivery form | Taped |
| Packaging unit | 5,000 pc(s). |
| Net weight | 5 kg |
| Gross weight | 0.656 kg |
| Customs tariff number | 85369010 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |
| ECLASS 8.0 | 36659290 |

© Rittal 2026

# Features

| | |
|---|---|
| Product description | Wire end ferrules 0.75 mm² x 10 mm AWG 18, packs of 5,000 pc(s)., colour: white, delivery form: on belt (in accordance with the Rittal colour code) |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |