Rittal – The System.

Faster – better – everywhere.



AS 4051.602

Wire end ferrule

State: 11/11/2026 (Source: www.rittal.com/us-en)

AS 4051.602 - Wire end ferrule on belt

With plastic flange.

Features

Model No.	AS 4051.602
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Yellow
Length	10 mm 0.39 ″
AWG	18
Internal diameter	3 mm 0.12 ″
Rittal color code	Yes
For cross section	1 mm²
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packaging unit	5,000 pc(s).
Net weight	5 kg
Gross weight	0.72 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

© Rittal 2026

Features

Product description	Wire end ferrules 1.0 mm² x 10 mm AWG 18, packs of 5,000 pc(s)., colour: yellow, delivery form: on belt (in accordance with the Rittal colour code)

Approvals

Approvals	UL + C-UL (listed)