

Rittal – The System.

Faster – better – everywhere.



AS 4052.104 Screwdriver

State: 4/15/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4052.104 - Screwdriver Insulated

With a long, slender handle and high-performance tip with insulation.

Features

| | |
|---------------------------|--|
| Model No. | AS 4052.104 |
| Version | With 1000 V protective insulation For slotted screws |
| Product description | With a long, slender handle and high-performance tip with insulation. |
| Benefits | Minimal force required, thanks to ergonomically styled handle Handle head with roll-off protection and clear screw marking Black coated blade tip to preserve precision and accuracy of fit Handle 30% and insulation up to 50% slimmer than that of a comparable tool Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working |
| Material | Blade: Chromium molybdenum vanadium alloy Inside of handle: Hard plastic Handle body: elastic, highly flexible plastic |
| Color | Handle: Anthracite and Rittal Power Pink |
| Blade dia. | 4 mm |
| Blade length | 100 mm |
| Blade (width x thickness) | 4 x 0.8 mm |
| Output | SL |
| Handle dia. | 25 mm |
| Handle length | 105 mm |
| Standards | IEC 60 900 |
| Packaging unit | 3 pc(s). |
| Net weight | 0.135 |
| Customs tariff number | 82054000 |

Features

| | |
|---------------------|----------------------------------|
| ETIM 9 | EC000144 |
| ETIM 8 | EC000158 |
| ECLASS 8.0 | 21040406 |
| Product description | Screwdriver insulated SL 4 x 0,8 |
