

Rittal – The System.

Faster – better – everywhere.



AS 4054.001 Crimping pliers

State: 4/29/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.001 - Crimping pliers For wire end ferrules

For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.



Features

Model No.	AS 4054.001
Version	Angled
Product description	For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.
Benefits	Minimal force required for large conductor cross-sections Pressing operation with a consistently high quality Labeled die stations for precise machining of the relevant cross sections Unlockable forced lock
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	Square crimp
Cable entry direction	At the front
Dimensions	Height: 59 mm Length: 198 mm Height: 2.32 " Length: 7.8 "
AWG	22 - 10

Features

For cross section	0.5 - 6 mm ²
Packaging unit	1 pc(s).
Net weight	0.452 kg
Gross weight	0.462 kg
Customs tariff number	82032000
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Product description	Crimping pliers for wire end ferrules