

Rittal – The System.

Faster – better – everywhere.



AS 4054.002 Crimping tool

State: 6/27/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.002 - Crimping tool For wire end ferrules

Crimping pliers for square or hexagonal compression for crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.

Features

Model No.	AS 4054.002
Version	Straight
Product description	For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.
Benefits	Minimal force required for large conductor cross-sections Pressing operation with a consistently high quality Unlockable forced lock Self-adjusting
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: RAL 7016 and RAL 35745
Crimping	Square crimp
Cable entry direction	Side
Dimensions	Length: 176 mm Length: 6.93 "
AWG	26 - 8
For cross section	0.14 - 10 mm ²
Packaging unit	1 pc(s).
Net weight	0.4 kg
Gross weight	0.449 kg
Customs tariff number	82032000
ETIM 9	EC000168

Features

ETIM 8	EC000168
ECLASS 8.0	21043811
Product description	AS crimping tool, square, for cross-section 0.14 – 10 mm ²
