

Rittal – The System.

Faster – better – everywhere.



AS 4054.004 Crimping pliers

State: 6/7/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.004 - Crimping pliers For wire end ferrules

For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.



Features

| | |
|-----------------------|---|
| Model No. | AS 4054.004 |
| Version | Straight |
| Product description | For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4. |
| Benefits | Minimal force required for large conductor cross-sections Pressing operation with a consistently high quality Labeled die stations for precise machining of the relevant cross sections Unlockable forced lock |
| Material | High-grade special tool steel |
| Surface finish | Matt, chromium-plated |
| Color | Handle: Anthracite and Rittal Power Pink |
| Crimping | WM crimp |
| Cable entry direction | Side |
| Dimensions | Height: 68 mm Length: 256 mm Height: 2.68 " Length: 10.1 " |
| AWG | 8 - 4 |
| For cross section | 10 - 25 mm ² |

Features

| | |
|-----------------------|---------------------------------------|
| Packaging unit | 1 pc(s). |
| Net weight | 0.66 kg |
| Gross weight | 0.69 kg |
| Customs tariff number | 82032000 |
| ETIM 9 | EC000168 |
| ETIM 8 | EC000168 |
| ECLASS 8.0 | 21043811 |
| Product description | Crimping pliers for wire end ferrules |