


# Rittal – The System.

Faster – better – everywhere.



## AS 4054.080 Crimping tool

State: 6/6/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.080 - Crimping tool For crimp tab terminals

For machining non-insulated tab receptacles



## Features

Model No.	AS 4054.080
Version	Angled
Product description	For crimping non-insulated crimp tab terminals.
Benefits	Unlockable forced lock Labeled die stations for precise machining of the relevant cross sections
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	B-crimp
Dimensions	Width: 18 mm Height: 59 mm Length: 198 mm Width: 0.71 " Height: 2.32 " Length: 7.8 "
AWG	26 - 16
For cross section	0.1 - 1.5 mm <sup>2</sup>
Packaging unit	1 pc(s).
Net weight	0.433

# Features

Gross weight	0.443
Customs tariff number	82032000
EAN	4028177807662
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811