

Rittal – The System.

Faster – better – everywhere.



SV 3439.010 Connection Adapters

State: 4/22/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3439.010 - Connection Adapters

For busbar systems with 60 mm center-to-center distance.

Features

| | |
|---|---|
| Model No. | SV 3439.010 |
| Material | Cover: ABS Chassis: Fiberglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0 |
| Color | RAL 7035 |
| Rated current max. | 600 A |
| Rated operating voltage | 690 V, 3~ |
| Cable outlet | Top/bottom |
| For bar systems with center-to-center spacing | 60 mm |
| Note | The technical data may vary for UL applications. UL approval only applies in conjunction with AC application The rated operating voltage for DC applications depends on the busbar arrangement in the busbar support 9340.050/9341.050/9342.050. |
| Number of poles | 3-pole |
| Dimensions | Width: 180 mm Height: 247 mm Width: 7.09 " Height: 9.72 " |
| Connection of round conductors, multi-wire | 35 - 240 mm ² |
| Suitable for busbars | Height: 5, 10 mm Height: 0.2, 0.39 " |
| Clamping area for laminated copper bars (W x H) | 24 x 21 mm 0.94 x 0.83 " |
| Packaging unit | 1 pc(s). |

Features

| | |
|------------------------------|---|
| Net weight | 4.36 kg |
| Gross weight | 4.635 kg |
| Copper weight (kg per piece) | 0.732 |
| Customs tariff number | 85369010 |
| ETIM 9 | EC001531 |
| ETIM 8 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Connection adaptor, 600 A, 690 V, 3-pole, cable outlet top/ bottom, round conductor connection 35-240 mm ² , clamping area WH: 24x21 mm |

Approvals

| | |
|--------------|---|
| Approvals | ABS |
| Explanations | Declaration of conformity Declaration of conformity UK |