
Rittal – The System.

Faster – better – everywhere.



SV 3458.500

Conductor terminal

State: 10/30/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 3458.500 - Conductor terminal

For connecting round conductors and laminated copper bars.

Features

Model No.	SV 3458.500
Product description	For connecting round conductors and laminated copper bars.
Material	Carbon steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	16.5 x 15 mm 0.65 x 0.59 ″
Note	Wire end ferrules should be used with fine stranded wire conductors
Connection of round conductors	35 - 70 mm²
For busbar thickness	10 mm 0.39 ″
Packaging unit	15 pc(s).
Net weight	1.65 kg
Gross weight	1.679 kg
PCF/VE (cradle-to-gate)	6.3 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	85369010
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146
Product description	SV Conductor connection clamp, 35-70 mm², clamping area WH: 16,5x15 mm, for bar thickness 10 mm

© Rittal 2026

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK