


# Rittal – The System.

Faster – better – everywhere.



## SV 3458.500

## Conductor terminal

State: 2/8/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



FRIEDHELM LOH GROUP

# SV 3458.500 - Conductor terminal

For connecting round conductors and laminated copper bars.

## Features

Model No.	SV 3458.500
Product description	For connecting round conductors and laminated copper bars.
Material	Carbon steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	16.5 x 15 mm 0.65 x 0.59 "
Note	Wire end ferrules should be used with fine stranded wire conductors
Connection of round conductors	35 - 70 mm <sup>2</sup>
For busbar thickness	10 mm 0.39 "
Packaging unit	15 pc(s).
Net weight	1.65
Gross weight	1.679
PCF/VE (cradle-to-gate)	6.3 kg CO <sub>2</sub> eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	85369010
EAN	4028177042766
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146

# Approvals

---

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK