

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.122**

**Round split plate punching machine**

State: 7/31/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.122 - Round split plate punching machine For stainless steel, with 3-way pitch

For punching round cut-outs

## Features

|  |   |
|--|---|
| Model No.  | AS 4055.122   |
| Version  | With 3-way split  |
| Product description  | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch. |
| Supply includes  | Die<br>Stamp  |
| Workable material  | Stainless steel   |
| Max. material thickness that can be machined for stainless steel | 2 mm  |
| Ø hole punch   | 22.5 mm   |
| Note   | Tension screws with a ball bearing must be used when operating with a wrench              |
| Suitable for hydraulic bolt order number                         | 4055.665  |
| Tension screw (Ø x L)  | 11.1 x 60 mm  |
| Hydraulic tension screw Ø  | 11.1 mm<br>19 cm  |
| Packaging unit   | 1 pc(s).  |
| Net weight   | 0.093   |
| Gross weight   | 0.113   |
| Customs tariff number  | 82073010  |
| EAN  | 4028177808010   |
| ETIM 9   | EC000156  |

# Features

|            |          |
|------------|----------|
| ETIM 8     | EC000156 |
| ECLASS 8.0 | 21049047 |