Rittal – The System.

Faster – better – everywhere.



SV 3565.005
Laminated Copper Bar




State: 11/7/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 3565.005 - Laminated Copper Bar

Cu lamina made of high-purity electrolyte copper, length: 2000 mm/bar.

Features

Model No.	SV 3565.005
Material	Cu lamina: High-purity electrolyte copper Insulation: Highly resistant vinyl blend, expansion 370%, temperature: -30°C ... +105°C, fire protection according to UL-94 V0, dielectric strength: 20 kV/mm
Length	2,000 mm 78.7 ″
Rated current for temperature increase 50 K	240 A
Rated current for temperature increase 30 K	180 A
Rated current for temperature increase 70 K	285 A
Note	Assembly = number of layers x layer width x layer thickness May be cut to length as required The conductor temperature of the laminated copper bar is derived by adding the ambient temperature and the temperature increase together. Example: 3565.005 carrying 180 A, i.e. the temperature increases by 30 K. At an ambient temperature of 35 °C, this produces a resultant conductor temperature of 35 °C + 30 K = 65 °C.

© Rittal 2026

Features

Laminated flat copper version	Number of lamina: 6 Lamina width: 9 mm Lamina thickness: 0.8 mm Lamina width: 0.35 ˝ Lamina thickness: 0.03 ˝
Packaging unit	1 pc(s).
Net weight	0.988 kg
Gross weight	1.188 kg
Copper weight (kg per piece)	0.77
Customs tariff number	85446010
ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303
Product description	SV Laminated copper bar, WH: 9x4,8 mm, L: 2000 mm

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK