Rittal – The System.

Faster – better – everywhere.



SV 3574.005 **Laminated Copper Bar**


State: 11/9/2025 (Source: rittal.com/us-en)



SV 3574.005 - Laminated Copper Bar

Cu lamina made of high-purity electrolyte copper, length: 2000 mm/bar.







Features

Model No.	SV 3574.005
Material	Cu lamina: High-purity electrolyte copper Insulation: Highly resistant vinyl blend, expansion 370%, temperature: -30°C +105°C, fire protection according to UL-94 V0, dielectric strength: 20 kV/mm
Length	2,000 mm 78.7 ″
Rated current for temperature increase 50 K	965 A
Rated current for temperature increase 30 K	730 A
Rated current for temperature increase 70 K	1,155 A

© Rittal 2025

Features

Note	Assembly = number of layers x layer width x layer thickness May be cut to length as required
	The conductor temperature of the laminated copper bar is derived
	by adding the ambient temperature and the temperature increase
	together. Example: 3565.005 carrying 180 A, i.e. the temperature
	increases by 30 K. At an ambient temperature of 35 °C, this produces a resultant conductor temperature of 35 °C + 30 K = 65 °C.
	produces a resultant conductor temperature of 35°C + 30 K = 65°C.
Laminated flat copper version	Number of lamina: 10
	Lamina width: 32 mm
	Lamina thickness: 1 mm
	Lamina width: 1.26 ″
	Lamina thickness: 0.04 ″
Packaging unit	1 pc(s).
Net weight	6.198
Gross weight	6.44
Copper weight (kg per piece)	5.73
Customs tariff number	74071000
EAN	4028177666801
ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3