
Rittal – The System.

Faster – better – everywhere.



SV 3582.020

Busbars CUPONAL


State: 11/9/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 3582.020 - Busbars CUPONAL

Copper-coated aluminum busbars.





Features

Model No.	SV 3582.020
Product description	Copper-coated aluminum busbars, suitable for configuring busbar systems with busbar supports SV 9340.000/SV 9340.050.
Material	Aluminum Copper
Rated current max.	235 A
Note	The rated current is generated at 65°C rail temperature and 35°C ambient temperature Correction factor diagram according to DIN EN 43 671 May be cut to length as required
Standards	DIN EN 13 601
Cross-section	20 mm x 5 mm 0.79 ″ x 0.2 ″
Dimensions	Length: 2,400 mm Length: 94.5 ″
Packaging unit	6 pc(s).
Net weight	4.5 kg
Gross weight	6.1 kg

Features

Copper weight (kg per piece)	0.35
Customs tariff number	76042990
ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303
Product description	SV Busbar CUPONAL, WH: 20x5 mm, L: 2400 mm

Approvals

Explanations	Declaration of conformity Declaration of conformity UK