

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.150**

**Round split plate punching machine**

State: 8/2/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.150 - Round split plate punching machine For stainless steel, with 3-way pitch

For punching round cut-outs

## Features

|  |  |
|--|--|
| Model No.  | AS 4055.150  |
| Version  | With 3-way split   |
| Supply includes  | Die<br>Stamp   |
| Workable material  | Stainless steel  |
| Max. material thickness that can be machined for stainless steel | 2.5 mm   |
| Ø hole punch   | 50.5 mm  |
| For thread   | M50  |
| Note   | Tension screws with a ball bearing must be used when operating with a wrench |
| Suitable for hydraulic bolt order number                         | 4055.663   |
| Tension screw (Ø x L)  | 19 x 75 mm   |
| Hydraulic tension screw Ø  | 19 mm  |
| Packaging unit   | 1 pc(s).   |
| Net weight   | 0.657  |
| Gross weight   | 0.731  |
| Customs tariff number  | 82073010   |
| EAN  | 4028177808126  |
| ETIM 9   | EC000156   |
| ETIM 8   | EC000156   |
| ECLASS 8.0   | 21049047   |