

**Rittal – The System.**

Faster – better – everywhere.



**IT 3659.181**

**Server telescopic slides**

State: 5/23/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# IT 3659.181 - Server telescopic slides for IT enclosure systems and IT enclosures

Ensure optimum accessibility to the server, even when built-in. For servers with a max. width of 430 mm.



## Features

Model No.	IT 3659.181
Version	For level spacing of 470.65 - 599.65 mm
Product description	Ensure optimum accessibility to the server, even when built-in. For servers with a max. width of 430 mm.
Material	Carbon steel
Load capacity	30 kg
Note	Only in conjunction with L-shaped profile rails
Suitable for	Enclosure type: TS TS IT VX VX IT Depth: = 600 mm Enclosure type: TS TS IT VX VX IT Depth: = 23.6 "
Packaging unit	2 pc(s).
Net weight	2.3 kg
Gross weight	2.62 kg

# Features

PCF/VE (cradle-to-gate)	5.1 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Product description	Server telescopic rails for TS, TS IT, VX, VX IT, for depth 600 mm, extension: 490 mm, for server with maximum width of 430 mm