

Rittal – The System.

Faster – better – everywhere.



AS 4055.220 Hole punch, round

State: 6/15/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.220 - Hole punch, round for carbon steel

For punching round cut-outs

Features

| | |
|--|--|
| Model No. | AS 4055.220 |
| Version | With 3 cutting tips |
| Supply includes | Die Stamp Tension screw without ball bearing |
| Workable material | Carbon steel |
| Max. material thickness that can be machined for sheet steel | 2 mm |
| Ø hole punch | 20.4 mm |
| For thread | M20 |
| Note | Tension screws with a ball bearing must be used when operating with a wrench Other sizes, see splitter hole punch, round, stainless steel |
| Suitable for hydraulic bolt order number | 4055.661 |
| Tension screw (Ø x L) | 9.5 x 50 mm |
| Hydraulic tension screw Ø | 9.5 mm 19 mm |
| Packaging unit | 1 pc(s). |
| Net weight | 0.102 kg |
| Gross weight | 0.122 kg |
| Customs tariff number | 82073010 |
| ETIM 9 | EC000156 |
| ETIM 8 | EC000156 |
| ECLASS 8.0 | 21049047 |

Features

Product description

Sheet metal punch round Ø 20,4 mm