

Rittal – The System.

Faster – better – everywhere.



HD 4000.064 Printer enclosure HD

State: 6/16/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.064 - Printer enclosure HD

Hygienically designed housing for installation of printers or other PC components in production areas

Features

Model No.	HD 4000.064
Benefits	For hygienic and safe installation of printers in production areas Can be combined with HD command panel to form a complete PC enclosure Device bases are removable and height adjustable for quick access to printer, e.g. for changing the labels
Material	Housing and door: Stainless steel 1.4301 (AISI 304) HD lock inserts: Stainless steel 1.4404 (AISI 316L) Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 Component shelf: Carbon steel, spray finished
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Seal: Blue, dyed (RAL 5010)
Supply includes	Housing of all-round solid construction Door with fitted seal Door hinged on the right, may be swapped to the left Component shelf
Options	Without side rails Without component shelf With mounting plate HD supporting structure with leveling
Dimensions	Width: 810 mm Height, front: 863 mm Height rear: 888 mm Depth: 496 mm Width: 31.9 " Height, front: 34 " Height rear: 35 " Depth: 19.5 "

Features

Material thickness - enclosure	1.5 mm 0.06 "
Material thickness - door	2 mm 0.08 "
Protection category IP to EN 60529	IP 66
Packaging unit	1 pc(s).
Net weight	54.2 kg
Gross weight	54.2 kg
PCF/VE (cradle-to-gate)	193.59
Customs tariff number	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Explanations	PCF-declaration
--------------	-----------------