

Rittal – The System.

Faster – better – everywhere.



AS 4050.150 Assembly frame

State: 7/8/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.150 - Assembly frame

The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for the mounting of plates and enclosures.

Features

Model No.	AS 4050.150
Version	150 MN (manually tilt-adjustable)
Product description	The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for the mounting of plates and enclosures.
Benefits	Allows ergonomic and back-friendly working Individually positionable in the workshop, as it is independent from the power network Minimal space required when not in use Easy handling thanks to four casters including complete locking function Variable fixing of mounting plates using quick-release fasteners
Technical specifications	Incline can be adjusted from approximately 0 – 80°
Supply includes	Assembly frame 1 VE clamping unit at bottom 1 packing unit with top clamping unit
Note	With the assembly frame extension, a maximum machining area of 1900 x 1900 mm can be achieved.
Machine dimensions	Width: 1,400 mm Depth: 1,250 mm
Dimensions support surface max.	Width: 1,110 mm Height: 1,900 mm
Dimensions support surface min.	Width: 1,110 mm Height: 1,230 mm
Load	150 kg 330.7 lb.

Features

Working height	Working height (min.): 100 cm Working height (max.): 100 cm
Packaging unit	1 pc(s).
Net weight	123 kg
Gross weight	138 kg
Customs tariff number	84279000
ETIM 9	EC002224
ETIM 8	EC002224
ECLASS 8.0	36659090
Product description	Assembly frame 150 MN

Approvals

Explanations	Declaration of conformity
--------------	---------------------------