

# Rittal – The System.

Faster – better – everywhere.



## AS 4055.249 Hole punch, round

State: 3/12/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.249 - Hole punch, round for carbon steel

For punching round cut-outs

## Features

|  |  |
|--|--|
| Model No.  | AS 4055.249  |
| Version  | With 3 cutting tips  |
| Supply includes  | Die<br>Stamp<br>Tension screw without ball bearing   |
| Workable material  | Carbon steel   |
| Max. material thickness that can be machined for sheet steel | 3 mm   |
| Ø hole punch   | 49.6 mm  |
| Note   | Tension screws with a ball bearing must be used when operating with a wrench<br>Other sizes, see splitter hole punch, round, stainless steel |
| Suitable for hydraulic bolt order number                     | 4055.663   |
| Tension screw (Ø x L)  | 19 x 75 mm   |
| Hydraulic tension screw Ø                                    | 19 mm  |
| Packaging unit   | 1 pc(s).   |
| Net weight   | 0.739 kg   |
| Gross weight   | 0.781 kg   |
| Customs tariff number  | 82073010   |
| ETIM 9   | EC000156   |
| ETIM 8   | EC000156   |
| ECLASS 8.0   | 21049047   |
| Product description  | Sheet metal punch round Ø 49,6 mm  |