

Rittal – The System.

Faster – better – everywhere.



AS 4055.512

Round split plate punching machine

State: 6/15/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.512 - Round split plate punching machine For sheet steel, with 3-way pitch

For punching round cut-outs

Features

Model No.	AS 4055.512
Version	With 3-way split
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Die Stamp
Workable material	Carbon steel
Max. material thickness that can be machined for sheet steel	1.5 mm
Ø hole punch	12.5 mm
For thread	M12
Note	Tension screws with a ball bearing must be used when operating with a wrench Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.660
Tension screw (Ø x L)	6 x 40 mm
Hydraulic tension screw Ø	6 mm 19 mm
Packaging unit	1 pc(s).
Net weight	0.034 kg
Gross weight	0.049 kg
Customs tariff number	82073010
ETIM 9	EC000156

Features

ETIM 8	EC000156
ECLASS 8.0	21049047
Product description	Splitter hole punch, round for sheet steel, with triple splitting
