

Rittal – The System.

Faster – better – everywhere.



AS 4050.318 Thread cutting option

State: 12/14/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.318 - Thread cutting option for Perforex LC 3030

Thread cutting option for Perforex LC laser center including thread tap with clamping units for M3 – M10.



Features

| | |
|--------------------------|---|
| Model No. | AS 4050.318 |
| Version | Moveable tool magazine with 6 magazine slots Tool holder Additional drive unit |
| Product description | Thread tapping option for the Perforex LC laser center. |
| Benefits | Machining of projects with tapped holes possible Fast, automatic changeover from laser function to thread cutting function by accommodating an additional machining head |
| Supply includes | Thread tap Including clamping units for M3 – M10 |
| Machinable height (max.) | 600 mm |
| Material thickness: | 5 mm 0.2 " |
| Suitable for Model No. | 4050330 |
| Packaging unit | 1 pc(s). |
| Net weight | 78 |
| Gross weight | 78 |
| Customs tariff number | 84669360 |
| EAN | 4028177806658 |
| ECLASS 8.0 | 36600890 |