## Rittal – The System.

Faster – better – everywhere.





# AS 4050.437 DIN support rail cutter MC3

State: 11/16/2025 (Source: rittal.com/us-en)



### AS 4050.437 - DIN support rail cutter MC3

Manual profile cutter for burr-free cutting of 30/15 C-profile rails as well as TS 35/7.5 and TS 35/15 support rails. The desired length of the rail can be precisely and repeatedly adjusted with the ruler (mm/inch) and the adjustable stop. For mounting on the workbench.



#### **Features**

Model No.	AS 4050.437
Product description	Manual profile cutter for burr-free cutting of 30/15 C-profile rails as well as TS 35/7.5 and TS 35/15 support rails. The desired length of the rail can be precisely and repeatedly adjusted with the ruler (mm/inch) and the adjustable stop. For mounting on the workbench.
Benefits	Cost-effective manual cutting of profile and mounting rails Easier to cut profile and support rails to the correct length than sawing by hand Easy burr-free cutting with eccentric lever Low-maintenance and durable
Support area	Width: 1,343 mm Height: 1,162 mm Depth: 312 mm Width: 52.9 " Depth: 12.3 "
Workable material	Carbon steel Aluminum Copper
Packaging unit	1 pc(s).
Net weight	15
Gross weight	16.15

© Rittal 2025 2

#### **Features**

Customs tariff number	73269098
EAN	4028177954021
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890

© Rittal 2025 3