Rittal – The System.

Faster – better – everywhere.





AS 4050.452 Crimping Machine L8

State: 11/10/2025 (Source: rittal.com/us-en)



AS 4050.452 - Crimping Machine L8

Electro-pneumatically driven wire stripping and crimping center that can process loose, insulated wire end ferrules.

Features

Model No.	AS 4050.452
Version	Touchscreen display
Product description	Electro-pneumatically driven wire stripping and crimping center that can process loose, insulated wire end ferrules.
Benefits	Easy operation
	Secure, fast processing of insulated wire end ferrules
	No set-up time thanks to automatic tool change
	Processing of special wires possible
	Simple, quick component mounting
	Automatic recognition of cross-sections
Technical specifications	Crimping range 0.5–2.5 mm² (AWG 20 - 14)
	Crimping length 8 mm (0.31 in.)
	Insertion length 35 mm (1.378 in.)
	Wire end ferrules with a plastic collar can be produced in special
	sizes
Supply includes	Crimping Machine L8
	1 swivel feeder bowl 0.5-1.5 mm²
	1 swivel feeder bowl 1.5–2.5 mm ²
Note	Standard crimping shape, trapezium - others available upon request
Dimensions	Width: 390 mm
	Height: 460 mm
	Depth: 330 mm
	Width: 15.4 "
	Height: 18.1 "
	Depth: 13 "
Compressed air connection	5.5 bar
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	110 VA

© Rittal 2025

Features

Crimping	Trapezoid crimp
Cycle time	1.5 s
Packaging unit	1 pc(s).
Net weight	34.6
Gross weight	34.67
Customs tariff number	84798997
EAN	4028177804869
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890

© Rittal 2025 3