

Rittal – The System.

Faster – better – everywhere.



AS 4050.452

Crimping Machine L8

State: 2/11/2026 (Source: ittal.com/us-en)



AS 4050.452 - Crimping Machine L8

Electro-pneumatically driven wire stripping and crimping center that can process loose, insulated wire end ferrules.

Features

Model No.	AS 4050.452
Version	Touchscreen display
Product description	Electro-pneumatically driven wire stripping and crimping center that can process loose, insulated wire end ferrules.
Benefits	<p>Easy operation</p> <p>Secure, fast processing of insulated wire end ferrules</p> <p>No set-up time thanks to automatic tool change</p> <p>Processing of special wires possible</p> <p>Simple, quick component mounting</p> <p>Automatic recognition of cross-sections</p>
Technical specifications	<p>Crimping range 0.5–2.5 mm² (AWG 20 - 14)</p> <p>Crimping length 8 mm (0.31 in.)</p> <p>Insertion length 35 mm (1.378 in.)</p> <p>Wire end ferrules with a plastic collar can be produced in special sizes</p>
Supply includes	<p>Crimping Machine L8</p> <p>1 swivel feeder bowl 0.5–1.5 mm²</p> <p>1 swivel feeder bowl 1.5–2.5 mm²</p>
Note	Standard crimping shape, trapezium - others available upon request
Dimensions	<p>Width: 390 mm</p> <p>Height: 460 mm</p> <p>Depth: 330 mm</p> <p>Width: 15.4 "</p> <p>Height: 18.1 "</p> <p>Depth: 13 "</p>
Compressed air connection	5.5 bar
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	110 VA

Features

Crimping	Trapezoid crimp
Cycle time	1.5 s
Packaging unit	1 pc(s).
Net weight	34.6
Gross weight	34.67
Customs tariff number	84798997
EAN	4028177804869
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890