

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.454

# Automatic Crimping Machine R8 E

State: 6/27/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.454 - Automatic Crimping Machine R8 E

Electrically driven wire stripping and crimping center that can process reel-mounted, insulated wire end ferrules.



## Features

Model No.	AS 4050.454
Version	Touchscreen display
Product description	Electrically driven wire stripping and crimping center that can process reel-mounted, insulated wire end ferrules.
Benefits	Easy operation Fast adjustment Flexible use in the workshop Fast replacement of consumables
Technical specifications	Cross-sections ranging from 0.5–2.5 mm <sup>2</sup> (AWG 20–14) Crimping length 8 mm (0.31 in.) Insertion length 40 mm (1.57 in.)
Note	Standard crimping shape, trapezium - others available upon request
Dimensions	Width: 288 mm Height: 230 mm Depth: 345 mm Width: 11.3 " Height: 9.06 " Depth: 13.6 "
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	100 VA
Crimping	Trapezoid crimp

# Features

Cycle time	1.8 s
Packaging unit	1 pc(s).
Net weight	16 kg
Gross weight	16 kg
Customs tariff number	84798997
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890
Product description	Crimp machine R 8E, 0,5-2,5mm <sup>2</sup>