

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.456

## Automatic Crimping Machine RC

State: 12/16/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.456 - Automatic Crimping Machine RC

Electro-pneumatic automatic crimping machine with five-fold magazine for processing insulated wire end ferrules in different cross-sections on coils.

## Features

Model No.	AS 4050.456
Version	Touchscreen display Selection of wire cross-section via touchscreen Support can be fitted with a maximum of 23,000 wire-end ferrules
Product description	
Benefits	Easy operation Secure, fast processing of insulated wire end ferrules No set-up time thanks to automatic tool change Simple, quick component mounting No need to change the wire-end ferrules thanks to the 5-way assembly
Technical specifications	Crimping range 0.5–2.5 mm <sup>2</sup> (AWG 20 - 14) 8 and 10 mm crimping lengths Insertion length 27 mm (1.06 in.)
Note	Standard crimping shape, trapezium - others available upon request
Dimensions	Width: 335 mm Height: 565 mm Depth: 485 mm Width: 13.2 " Height: 22.2 " Depth: 19.1 "
Compressed air connection	5.5 bar
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	16 VA
Crimping	Trapezoid crimp
Cycle time	2 s

# Features

Packaging unit	1 pc(s).
Net weight	24.8
Gross weight	25.4
Customs tariff number	84624900
EAN	4028177930865
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	17130101