


Rittal – The System.

Faster – better – everywhere.



AS 4050.749 Wire end ferrule

State: 9/8/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.749 - Wire end ferrule on belt

With plastic flange.

Features

Model No.	AS 4050.749
Version	For assembly machines
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Black
Suitable for	Enclosure type: Automatic crimping machine RC Automatic crimping machine R8 Automatic crimping machine R8 E
Length	8 mm 0.31 "
AWG	16
Internal diameter	3.5 mm 0.14 "
For cross section	1.5 mm ²
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Delivery form	Taped
Packaging unit	5,000 pc(s).
Net weight	5
Gross weight	0.722
Customs tariff number	85369010

Features

EAN	4028177805170
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------