


# Rittal – The System.

Faster – better – everywhere.



## AS 4050.750 Wire end ferrule

State: 7/25/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.750 - Wire end ferrule on belt

With plastic flange.

## Features

|                          |  |
|--------------------------|--|
| Model No.                | AS 4050.750  |
| Product description      | With plastic flange.   |
| Technical specifications | Heat resistant up to 105 °C  |
| Material                 | E-Cu, tin-plated<br>Plastic collar: Polypropylene                            |
| Color                    | Blue   |
| Length                   | 8 mm<br>0.31 ~   |
| AWG                      | 14   |
| Internal diameter        | 4.2 mm<br>0.17 ~   |
| For cross section        | 2.5 mm <sup>2</sup>  |
| DIN color code           | Yes  |
| Note                     | UL-certified in conjunction with the relevant tools, e.g. crimping machines. |
| Standards                | AEH DIN 46228  |
| Delivery form            | Taped  |
| Packaging unit           | 3,000 pc(s).   |
| Customs tariff number    | 85369010   |
| EAN                      | 4028177805187  |
| ETIM 9                   | EC000005   |
| ETIM 8                   | EC000005   |
| ECLASS 8.0               | 36659290   |

# Approvals

---

Approvals

UL + C-UL (listed)

UR