
### Rittal – The System.

Faster – better – everywhere.





# AS 4050.750 Wire end ferrule

State: 11/16/2025 (Source: rittal.com/us-en)



#### AS 4050.750 - Wire end ferrule on belt

With plastic flange.

#### **Features**

Model No.	AS 4050.750
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Blue
Length	8 mm 0.31 ~
AWG	14
Internal diameter	4.2 mm 0.17 ″
For cross section	2.5 mm²
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packaging unit	3,000 pc(s).
Net weight	3
Customs tariff number	85369010
EAN	4028177805187
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

© Rittal 2025

## Approvals

Approvals

UL + C-UL (listed)

UR

© Rittal 2025 3