
Rittal – The System.

Faster – better – everywhere.



AS 4051.599

Wire end ferrule

State: 11/11/2026 (Source: www.rittal.com/us-en)

AS 4051.599 - Wire end ferrule on belt

With plastic flange.

Features

Model No.	AS 4051.599
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	White
Length	8 mm 0.31 ″
AWG	18
Internal diameter	2.8 mm 0.11 ″
Rittal color code	Yes
For cross section	0.75 mm²
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packaging unit	5,000 pc(s).
Net weight	5 kg
Gross weight	0.598 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

© Rittal 2026

Features

Product description	Wire end ferrules for crimping machines, 0.75 mm², AWG 18, 8 mm, orange, on belt, 5000 pc(s).

Approvals

Approvals	UL + C-UL (listed) UR