

# Rittal – The System.

Faster – better – everywhere.



## AS 4055.720 Electro-hydraulic pump

State: 4/2/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.720 - Electro-hydraulic pump

The electro-hydraulic pump is used to drive the products from the CW 120-S product range.



## Features

Model No.	AS 4055.720
Product description	The electro-hydraulic pump is used to drive the products from the CW 120-S product range.
Rated power	1.3 kW
Filling volume	3.2 l
Working volume	2.2 l
Flow rate (max.)	1.1 l/min
Oil (type)	HLP 46
Rated operating voltage	230 V, 50 Hz
Rated current	5.65 A
Machine dimensions	Width: 400 mm Height: 325 mm Depth: 335 mm
Support area	Width: 402 mm Height: 342 mm Depth: 397 mm Width: 15.8 " Depth: 15.6 "
Permissible operating pressure (p. max.)	700 bar 10,152.6 PSI
Packaging unit	1 pc(s).

# Features

---

Net weight	32 kg
Gross weight	34.5 kg
Customs tariff number	84138100
ETIM 9	EC011047
ETIM 8	EC011047
ECLASS 8.0	27301290
Product description	Electro-hydraulic pump suitable for CW 120 – S and hydraulic cylinders

# Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------