Rittal – The System.

Faster – better – everywhere.





AS 4055.800 Busbar processing CW 120-M

State: 11/15/2025 (Source: rittal.com/us-en)



AS 4055.800 - Busbar processing CW 120-M

The mobile product solution for processing busbars is suitable for precise, quick, and ergonomic bending, punching, and cutting of busbars directly at the relevant workstation. The integrated precision laser makes the cutting and bending process easier.







Features

Model No.	AS 4055.800
Version	Electrical protractor
	Mandrel R10
	Bending die
	External 230 V power connection
	Laterally-removable support extension for long rails
	External hydraulic connection for almost all machining possibilities
	4 casters (2 lockable)
	Drawer runners
	Integrated hydraulic pump
	Laser pointer (auxiliary laser) beam power, laser class 1
	Pull-out length stop
Product description	The mobile product solution for busbar machining is ideal for
	precise, fast and ergonomic bending, punching and cutting of
	busbars directly at your workstation. The integrated precision laser
	makes the cutting and bending process easier. The integrated
	precision laser makes the cutting and bending process easier.
Benefits	High level of bending and punching accuracy
	Simple tool change
	Flexible use in the workshop
Supply includes	Busbar processing mobile CW 120-M
	Foot switch

© Rittal 2025

Features

Workable material	Copper Aluminum
Note	Leg length at a Z-bend depends on the material thickness For punching, slots of up to a max. of 21 x 18 mm are also supported Slot tools available on reques We reserve the right to make technical modifications
Machine dimensions	Width: 1,380 mm Height: 1,270 mm Depth: 945 mm
Contact surface	Width: 1,211 mm Depth: 811 mm Width: 47.7 " Depth: 31.9 "
Working height	974 mm
Rated power	2.2 kW
Rated operating voltage	230 V, 50 Hz/60 Hz
Length stop (max.)	1,224 mm
Bending/Leg length (min.)	50 mm
Bending angle (max.)	90 °
Bending (max.)	120 x 12 mm
Z-Bend (min.)	72 mm
Cutting (max.)	120 x 12 mm
Stamping (max.)	6.6 x 21.5 mm
Stamping/material thickness (max.)	12 mm 0.47 ″
Permissible operating pressure (p. max.)	700 bar 10,152.6 PSI
Packaging unit	1 pc(s).
Net weight	473
Gross weight	493

© Rittal 2025 3

Features

Customs tariff number	84624900
EAN	4028177920637
ETIM 9	EC011824
ETIM 8	EC011824
ECLASS 8.0	36600804

Approvals

Explanations Declaration of conformity

© Rittal 2025