## Rittal – The System.

Faster - better - everywhere.





# AS 4052.106 Screwdriver

State: 11/5/2025 (Source: rittal.com/us-en)



## AS 4052.106 - Screwdriver Insulated

With a long, slender handle and high-performance tip with insulation.

#### **Features**

Model No.	AS 4052.106	
Version	With 1000 V protective insulation For slotted screws	
Product description	With a long, slender handle and high-performance tip with insulation.	
Benefits	Minimal force required, thanks to ergonomically styled handle Handle head with roll-off protection and clear screw marking Black coated blade tip to preserve precision and accuracy of fit Handle 30% and insulation up to 50% slimmer than that of a comparable tool Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working	
Material	Blade: Chromium molybdenum vanadium alloy Inside of handle: Hard plastic Handle body: elastic, highly flexible plastic	
Color	Handle: Anthracite and Rittal Power Pink	
Blade dia.	5.5 mm	
Blade length	125 mm	
Blade (width x thickness)	5.5 x 1 mm	
Output	SL	
Handle dia.	27 mm	
Handle length	115 mm	
Standards	IEC 60 900	
Packaging unit	3 pc(s).	
Customs tariff number	82054000	
EAN	4028177807235	

© Rittal 2025

### **Features**

ETIM 9	EC000144	
ETIM 8	EC000158	
ECLASS 8.0	21040406	

© Rittal 2025 3