

Rittal – The System.

Faster – better – everywhere.



TS 4162.000 Threaded blocks

State: 6/10/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4162.000 - Threaded blocks

Used on enclosures and rails with rectangular 12.5 x 10.5 mm system punching with snap-off insertion aid, made from die-cast zinc.



Features

Model No.	TS 4162.000
Product description	With snap-off insertion aid, made from die-cast zinc.
Installation options	<ul style="list-style-type: none">On the horizontal and vertical VX enclosure sectionOn the vertical TS, VX SE enclosure section via adapter rail for VX compatibilityOn the horizontal TS enclosure sectionOn the horizontal VX SE enclosure section, bottomOn the horizontal VX SE enclosure section top, in depthOn punched rails 23 x 23 mmOn mounting chassis 23 x 73 mmOn mounting chassis 45 x 88 mmOn 23 x 64 mm system chassisOn 23 x 73 mm system chassisOn 23 x 89 mm system chassis, stainless steelOn enclosures and rails with rectangular hole profile 12.5 x 10.5 mm
Dimensions	Thread: M6
Suitable for enclosure type	<ul style="list-style-type: none">VXTSVX SE
Thread	M6
Packaging unit	50 pc(s).
Net weight	0.45 kg

Features

Gross weight	0.5 kg
Customs tariff number	73181692
ETIM 9	EC002358
ETIM 8	EC002358
ECLASS 8.0	23110815
Product description	TS Threaded block, for thread M6
