

# Rittal – The System.

Faster – better – everywhere.



## TS 4309.000 Support Strip

State: 9/9/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 4309.000 - Support Strip for VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



## Features

Model No.	TS 4309.000
Product description	For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.
Technical specifications	4.5 mm diameter hole on a 25 mm hole pattern
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Length	390 mm 15.4 "
Suitable for door width	500 mm 19.7 "
Installation options VX	In door width 500 mm
Installation options VX SE	In door width 500 mm In enclosure depth 400 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility
Installation options AX	In door width 500 mm, with 3-point locking system in the locking door In enclosure width 400 mm and in enclosure height 500 mm, in conjunction with rail for interior installation AX

# Features

Installation options AX stainless steel	In enclosure width + 400 mm In enclosure height/width 500 mm
Installation options AX plastic	In door width 500 mm
Installation options for 3-part AX	Enclosure depth 573 mm
Installation options TS	In door width 500 mm In enclosure width/depth 400 mm on the inner mounting level
Installation options TP	In consoles for 3-part assembly, at the height of the enclosure cover, in conjunction with rail for interior installation for TP, compact enclosure HD
Installation options VX base/plinth, stainless steel	In base/plinth depth 500 mm, in conjunction with M6 hexagon socket screws and M6 nuts
Suitable for	Enclosure type: VX TS VX SE TP AX AX plastic AX wall-mounted housing, 3-part Suitable for width/depth: 400 mm Enclosure type: VX TS VX SE TP AX AX plastic AX wall-mounted housing, 3-part Suitable for width/depth: 15.7 "
Suitable for	VX base/plinth system, stainless steel
Packaging unit	20 pc(s).
Net weight	3.78
Gross weight	4.1
PCF/VE (cradle-to-gate)	15.2 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared

# Features

Customs tariff number	73269098
EAN	4028177098510
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261