

**Rittal – The System.**

Faster – better – everywhere.



**VX 4333.180**

**Cross-brace for mounting plates**

State: 4/22/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 4333.180 - Cross-brace for mounting plates for VX, TS, VX SE

Additional horizontal cross braces to dampen vibrations and/or for retrospective stabilization of wide mounting plates. The struts can also be used as an additional aid to secure heavy structural elements.



## Features

|                     |   |
|---------------------|---|
| Model No.           | VX 4333.180   |
| Product description | Additional horizontal cross braces to dampen vibrations and/or for retrospective stabilization of wide mounting plates. The braces can also be used as an additional aid to secure heavy structural elements. |
| Material            | Carbon steel  |
| Surface finish      | Zinc-plated   |
| Supply includes     | 2 sections<br>4 clamps<br>4 grub (set) screws M10 x 16 mm   |
| Note on Model No.:  | Other widths available on request.  |
| Suitable for        | Enclosure type: VX<br>TS<br>VX SE<br>Width: = 1,800 mm<br>Enclosure type: VX<br>TS<br>VX SE<br>Width: = 70.9 "  |

# Features

|                                     |  |
|-------------------------------------|--|
| Packaging unit                      | 2 pc(s).   |
| Net weight                          | 7.414 kg   |
| Gross weight                        | 7.804 kg   |
| PCF/VE (cradle-to-gate)             | 29.7 kg CO2 eq (Cat B)   |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number               | 73269098   |
| ETIM 9                              | EC002625   |
| ETIM 8                              | EC002625   |
| ECLASS 8.0                          | 27189234   |
| Product description                 | VX cross-brace for mounting plates, for TS, SE, for W: 1800 mm   |