

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.003 Crimping tool

State: 5/27/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.003 - Crimping tool For wire end ferrules

Crimping pliers for square or hexagonal compression for crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.

## Features

Model No.	AS 4054.003
Version	Straight
Product description	For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.
Benefits	Minimal force required for large conductor cross-sections Pressing operation with a consistently high quality Unlockable forced lock Self-adjusting
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	Hexagonal crimp
Cable entry direction	Side
Dimensions	Length: 176 mm Length: 6.93 "
AWG	26 - 8
For cross section	0.14 - 10 mm <sup>2</sup>
Packaging unit	1 pc(s).
Net weight	0.4 kg
Gross weight	0.455 kg
Customs tariff number	82032000
ETIM 9	EC000168

# Features

---

ETIM 8	EC000168
ECLASS 8.0	21043811
Product description	AS crimping tool, hexagon, for cross-section 0.14 – 10 mm <sup>2</sup>

---