Rittal – The System.

Faster – better – everywhere.



AS 4054.003 Crimping tool

State: 11/18/2025 (Source: rittal.com/us-en)



AS 4054.003 - Crimping tool For wire end ferrules

Crimping pliers for square or hexagonal compression for crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.

Features

Model No.	AS 4054.003
Version	Straight
Product description	For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.
Benefits	Minimal force required for large conductor cross-sections Pressing operation with a consistently high quality Unlockable forced lock Self-adjusting
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	Hexagonal crimp
Cable entry direction	Side
Dimensions	Length: 176 mm Length: 6.93 "
AWG	26 - 8
For cross section	0.14 - 10 mm²
Packaging unit	1 pc(s).
Net weight	0.4
Gross weight	0.455
Customs tariff number	82032000
EAN	4028177930964

© Rittal 2025 2

Features

ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811

© Rittal 2025 3