

Rittal – The System.

Faster – better – everywhere.



SZ 4944.000

C rails 30/15

State: 12/14/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4944.000 - C rails 30/15 to EN 60 715 for VX, TS, VX SE

For direct mounting on the horizontal enclosure profile or vertical enclosure profile using additional fastening components.



Features

| | |
|------------------------------|---|
| Model No. | SZ 4944.000 |
| Material | Carbon steel |
| Surface finish | Zinc-plated |
| Length | 555 mm 21.9 " |
| Installation options | On the inner mounting level, on VX enclosure profile On the vertical TS, VX SE enclosure section via snap-on nuts TS 8800.808 or adapter rail for VX compatibility On the horizontal VX SE enclosure profile in the width bottom and top On the horizontal VX SE enclosure section in depth at the bottom (without mounting plate) and at the top using snap-on nut 8800.808 On the horizontal TS enclosure section In the width or depth of the 3-part AX. Depending on the installation situation, the rail must be shortened to the desired length. |
| Installation options VX Base | In base/plinth width 600 mm on the base/plinth panels, in conjunction with retaining/spacer piece |
| installation options AX Base | In base/plinth width 600 mm, in conjunction with hexagon socket tapping screws |

Features

| | |
|-------------------------------------|--|
| Suitable for | Enclosure type: VX TS AX wall-mounted housing, 3-part Width/depth: 600 mm Enclosure type: VX TS AX wall-mounted housing, 3-part Width/depth: 23.6 ~ |
| Suitable for | AX base/plinth system VX base system |
| Packaging unit | 6 pc(s). |
| Net weight | 2.118 |
| Gross weight | 2.4 |
| PCF/VE (cradle-to-gate) | 9.1 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73269098 |
| EAN | 4028177114593 |
| ETIM 9 | EC000386 |
| ETIM 8 | EC000386 |
| ECLASS 8.0 | 27400602 |