

Rittal – The System.

Faster – better – everywhere.



AS 4054.023 Crimping pliers

State: 1/2/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.023 - Crimping pliers For cable lugs

For use with non-insulated ring terminals



Features

Model No.	AS 4054.023
Version	Straight
Product description	For crimping non-insulated ring terminals.
Benefits	Unlockable forced lock Thanks to optimized lever transmission, only minimal actuation forces are required even for larger cross-sections
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	Double-indent crimp
Dimensions	Height: 68 mm Length: 256 mm Height: 2.68 " Length: 10.1 "
AWG	12 - 8
For cross section	4 - 10 mm ²
Packaging unit	1 pc(s).
Net weight	0.63
Gross weight	0.668

Features

Customs tariff number	82032000
EAN	4028177807648
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811